


VITALITY TOTAL LIGHT³





VITALITY TLT

- RED LIGHT, BLUE LIGHT, & UV
- RED LIGHT ONLY SESSION POSSIBLE
- SPECTRA FACIAL & SHOULDER TANNER
- CUSTOMIZABLE PERSONAL SUNSTYLE

Ergoline

VITALITY | TOTAL LIGHT TECHNOLOGY STANDARD DESIGN



Total Light Technology represents a new era in combined UV and light technology. This combination of Red Light, Blue Light and UV provides optimal tanning results and high levels of client customization to each and every session. Your customers demand the very best and Total Light Technology is here to meet increasing demands for innovation and individualized results. The addition of Blue Light enhances the tanning environment and provides an energizing experience during a session.

ERGOLINE, A BRAND OF JK PRODUCTS & SERVICES, INC.

411 West Washington Avenue, Suite B | Jonesboro, AR 72401

Toll-free: 888.771.0996 | www.jkproducts.us

| | |
|--|---|
| Technology | Total Light Technology TLT |
| Tanning Time | 10 minutes |
| Red & Blue LEDs | Face & Body: 24 x Red LEDs + 24 x Blue LEDs Body: 30 x Red LEDs + 30 x Blue LEDs |
| Low pressure lamps | 36 x 200 W Genesis PLT 14 x 200 W Genesis HLT |
| Dynamic vs. Static electronic ballasts | Dynamic electronic ballasts |
| LED Facial tanner | Spectra LED facial tanner: 168 x UVA LEDs |
| Spaghetti lamps Facial tanner | 4 x 8 W Genesis HLT |
| LED Shoulder Tan | 40 x UVA LEDs |
| Choice of UV intensity UV-Free treatment | Sensitive, Medium, Intensive UV-free treatment is possible |
| Air conditioning | AC + Temptronic |
| Ventilation | Surround Cooling Plus 3-zone ventilation |
| Aqua Mist / Aroma | ✓ / ✓ |
| Sound | Cinematic Sound |
| Smart phone connection | Bluetooth® Connect |
| Smart phone wireless charging station | ✓ (o) |
| Acrylic base | Multi Relax (87 x 46 in) |
| External display | Exterior 10" Touch Display incl. video function |
| Internal display | Interior 7" touch display |
| NFC Connect | ✓ |
| Voice Guide | ✓ |
| Set-up Manager | Professional Set-up Manager Plus |
| Remote Access | ✓ |
| Service Light | ✓ |
| Color | Glossy pearl white |
| Decor Styling | ✓ (o) |
| External lighting | LED Light Show (dynamic) |
| Ambient backlight | ✓(Dynamic) |
| Internal lighting | LED Interior Light |
| Dimensions closed | 92 x 57 x 61 |
| Dimensions open (L x W x H in) | 92 x 57 x 74 |
| Unit footprint (L x W in) | 99 x 91 |
| Room size rec. (L x W ft) | 10 x 9 |
| Max. power consumption with 400/415 V 3N power supply | 14,600 W |
| Fuse (delayed action) | 60 amp 3 phase 90 amp 2 phase |
| Weight | 1,554 lb |

CONTRAINDICATIONS:

Follow Instructions. Avoid over-exposure as with natural sunlight. Over-exposure can cause eye or skin injury and allergic reactions. Repeated exposure may cause premature aging of the skin and skin cancer. ALWAYS WEAR PROTECTIVE EYEWEAR! Failure to do so may result in severe burns or long term injury to the eyes. Certain medications or cosmetics may increase your sensitivity to ultraviolet radiation. Consult a physician before using sunlamps if you are using medication, have a history of skin problems or believe yourself to be especially sensitive to sunlight. If you do not tan in the sun, you are unlikely to tan from the use of this product. Please refer to the recommended exposure schedule for your skin type and do not tan more than once in a 24-hour period. Attention: This sunlamp product should not be used on persons under the age of 18 years. Persons who should not use this device include anyone who is sunburned, has open wounds, is naturally pale, has discolored patches of skin, has an increased risk of skin cancer, is being treated for or taking medicine causing photosensitivity, is pregnant, has atypical moles or more than 16 moles on their body (2mm diameter or larger). © 2020 JK Products & Services, Inc.